



PRODUCT SUMMARY

A system is defined by its weakest link. Even something as small as the feel of a trackpad is scrutinized to make sure it delivers optimal performance to the end user. In this application, FUTEK's LSB200 is fixed onto a testing actuator to record tactile feedback, run cycle test and quantify the force required to stimulate touchpad response.

PRODUCTS IN USE

Miniature S-Beam Jr. (LSB200) paired with Instrumentation (USB220).

All FUTEK application illustrations are strictly conceptual. Please contact us with questions.